THE CORROSION PROPERTIES OF MULTILAYER COATINGS DEPOSITED ON STAINLESS STEEL AND TI4AI6V SUBSTRATES

A. Zykova, V. Safonov¹, J. Walkowich², R. Rogowska², S. Yakovin³

Institute of Surface Engineering, Kharkov, Ukraine, E-mail: zykov@bi.com.ua;

¹NSC "Kharkov Institute of Physics and Technology", Kharkov, Ukraine;

²Institute for Sustainable Technologies, National Research Institute, Radom, Poland;

³ V.N. Karazin Kharkov National University, Department of Physical Technologies,

Kharkov, Ukraine;

Stainless steel (SS), titanium (Ti) and its alloys are the most widely used for clinical applications. The surface modification of metals with ceramic coatings by means of modern plasma methods is perspective way to reduce corrosion, to achieve better biocompatibility and to improve the performance of medical devices. The comparative analysis of the TiN, ZrO₂, Al₂O₃ and multilayer nitride/oxide coatings adhesion properties, hardness, elastic modulus, thickness, and corrosion resistance parameters at 05 N NaCl and SBF solution was made. PACS: 87.80.Rb

1. INTRODUCTION

The ceramic coatings play an important role in the surface modification of tools and instruments for various industrial sectors. However, many of such applications require the high stability in an aggressive and corrosive environment. Corrosion is one of the major processes that cause problems when metals and alloys are used as implants in the body [1]. Corrosion of implants in the aqueous medium of body fluids takes place via electrochemical reactions [2] and it is necessary to understand the electrochemical principles that are most relevant to the corrosion processes. The body fluid environment may well decrease the fatigue strength of the metal implant and enhance the release of iron, chromium, nickel, titanium ions and these ions are found to be powerful allergens and carcinogens [3]. The presence of titanium in the surrounding tissues of these implants in the form of titanium compounds and subsequent failure of implants due to fatigue, stress corrosion cracking and poor wear resistance have been reported [4,5]. Release of metal ions into the tissues adjacent to the implants results in accumulation of harmful products at tissue and internal organs of animals [6]. This may also be detrimental to the bone attachment and further bone growth on the implant surface.

2. MATERIALS AND METHODS

At present study the comparative analysis of parameters for various coating types such as TiN, deposited by means Arc-PVD technology, oxide ZrO₂ coatings deposited by EB-PVD technology and Al₂O₃ films deposited by magnetron sputtering (MS) method and also multilayer TiN/ZrO₂, TiN/Al₂O₃ on the stainless steel (1H18N9) and titanium-based material (Ti4Al6V) has been made. The main parameters of the process of TiN (Arc-PVD) coatings deposition were described in our previous study [6]. The Al₂O₃ (MS) and multilayer coating deposition was performed in high vacuum pumping system with the base pressure about 10⁻⁵ mBar. The main details of the magnetron and ion source in the sputtering chamber were demonstrated at [7]. The coatings adhesion properties, hardness and elastic

modulus, thickness were evaluated by standard methods. The corrosion examinations of anodic polarization by potentiodynamic method at the potential -1.0V...+2.0V with scanning rate 1mv/s, -0.050V...+0.050V and Stern - -0.020V...+0.020V range curves and also impedance method for frequency range 100 kHz...10 MHz at 0.5 N NaCl and SBF(NaCl-8,035, NaHCO₃-0,355, KCl-0,225, K₂HPO₄ 3H₂O-0,231, MgCl₂ 6H₂O-0,311, CaCl₂-0,292, Na₂SO₄-0,072 at pH=7.4 and temperature 37°C) solutions were made by Potentiostat PARSTAT 2263 (AMETEK, USA). The samples were immersed in the electrolyte and the potential was monitored as a function of time until the potential reached a stable value. Corrosion in the form of anodic dissolution occurs at solution like uniform removal process for substrates and corrosive electrolyte pore penetration process for ceramic coatings.

Electrochemical Impedance Spectroscopy (EIS) is a powerful analysis technique, which can provide a lot of information on the corrosion reactions, the mass transport and electrical charge transfer characteristics of coated materials in various solutions. The impedance spectrum dielectric behaviour, oxidation-reduction reflects reactions and mass migration which are determined by the electrical and chemical properties of the corrosion medium and the electrode materials. Over a frequency bandwidth of interest the impedance was presented in various ways by both the Nyquist and Bode plots. EIS spectra describe the electrical charge transfer kinetics and details of physical and electrochemical corrosion characteristics of substrate/coating interface. measurements were obtained in 0.5 N NaCl and SBF solution. Platinum wire and Ag/AgCl were used as counter and reference electrodes, respectively between the frequency ranges 100 kHz...10 MHz at constant 5 mV amplitude and 250 mV initial potential parameters measurements. The impedance |Z|polarisation resistance Rp and capacitance C were calculated from Nyquist and Bode plots. The surface topography before and after corrosion test was investigated by SEM (HITACHI, Japan) and AFM (Quesant Instrument Corporation, USA).

156

3. RESULTS AND DISCUSSION

The coatings adhesion properties, hardness and elastic modulus are presented at the Table.

The mechar	ıical proper	ties of coat	ings d	leposited	on
SS()	1H18N9) ar	ıd Ti alloy (Ti4Al	(6V)	

Coatings	Mechanical properties					
type	(average results 10 tests)					
	Hardness,	Hardness,	Young	Adhesion,		
	Hv	H[Mpa]	Modul.	[N]		
			[Gpa]			
SS/TiN	2051.6	22138.8	411.6	80.4		
SS/ZrO ₂	429.5	4634.5	96.7	38.3		
SS/ Al ₂ O ₃	752.0	8115.2	209.4	40.1		
SS/TiN/Al ₂ O ₃	797.36	8604.4	216.5	86.7		
Ti/TiN	1935.2	20893.2	340.8	29.3		
Ti/ZrO ₂	136.5	1472.4	49.3	13.4		
Ti/ Al ₂ O ₃	953.6	8289.9	172.0	27 .1		
Ti/TiN/Al ₂ O ₃	970.1	8523.2	177.7	39,9		

The best mechanical parameters were obtained in the case of nitride coatings both at SS and Ti substrates and also for multilayer nitride/oxide coatings.

The corrosion tests of anodic polarization by potentiodynamic method at the potential range -1.0V...+2.0V with scanning rate 1mv/s were presented in Fig.1 for SS, SS/TiN,SS/ZrO₂, SS/ Al₂O₃ (at NaCl, Fig.1a, and SBF, Fig.1b, solutions) and Fig. 2 for Ti, Ti/TiN, Ti/ZrO₂, Ti/Al₂O₃ (at NaCl – Fig.2a and SBF–Fig. 2b solutions) coatings by Tafel -0.050V...+0.050V and Stern – -0.020V...+0.020V range curves.





Fig.1. The anodic polarization curves for coatings at: a) 0.5 N NaCl and b) SBF solutions; SS-1, SS/TiN-2, SS/ZrO₂-3 and SS/Al₂O₃-4






Fig.2. The anodic polarization curves for coatings at a) 0.5 N NaCl and b) SBF solutions; Ti-1, Ti/TiN-2, Ti/ZrO2-3 and Ti/Al2O3-4

The impedance spectra of all the samples were recorded before and after polarization conditions, to evaluate the performance of the coatings under equilibrium conditions and after the onset of the corrosion process respectively. The Nequist plot of impedance was obtained from real $(Z_{re} = R_s + R_p/(1 + \omega^2 R_p^2 C_d^2))$ and imaginary $(Z_{im} = \omega R_p^2 C_d^2/(1 + \omega^2 R_p^2 C_d^2))$ impedance at different frequencies to determine charge-transfer kinetics (R_s is electrolyte solution resistance, R_p is polarization resistance and C_d is capacitance at interface). Fig. 3a and 3b show the Nyquist plots for SS, SS/Al₂O₃ and in for Ti, Ti/Al₂O₃ coatings at SBF solution. The data show that coating deposition had improved charge-transfer kinetic performance in counter electrode-electrolyte interfaces. The surface with ceramic oxide coatings has strong capacitive response due to their electrically inert properties and high dielectric constants. The surface topography before and after corrosion tests was investigated by SEM and AFM methods. The Fig. 4 (SS, SS/TiN, SS/TiN/Al₂O₃, at 0.5 N NaCl SEM) data further confirmed the main results of polarization curves and EIS measurements.




Fig.3. Nyquist plots for a) SS, SS/Al₂O₃ and b)Ti, Ti/Al2O3 coatings at SBF solution




Fig.4. SS, SS/TiN, SS/TiN/Al₂O₃ at 0.5 N NaCl SEM

4. CONCLUSIONS

The results show that the best mechanical parameters were obtained for the nitride coatings both on the stainless steel (1H18N9) and the titanium substrate (Ti4Al6V). However, the nitride corrosion resistances were less on 1H18N9 than on Ti4Al6V and less than those obtained

for oxide coatings deposited by both methods. The best corrosion resistance characteristics at NaCl and SBF solutions demonstrate the multilayer coatings TiN/ZrO₂, TiN/Al₂O₃ both on stainless steel and titanium substrates.

REFERENCES

- 1. E. Eisenbarth, D. Velten, K. Schenk-Meuser, P. Linez, V. Biehl, H. Duschner, J. Breme, H.F. Hildebrand. Interactions between Cells and Titanium Surfaces// *Biomolecular Engineering*. 2002, v. 19, p. 243-49.
- 2. L. Dion, F. Bordenave, R. Lefebvre, C.V. Boreille et al. Physico-Chemistry and Cytotoxicity of Ceramics// *Journal of Materials Science: Materials in Medicine*. 1994, v.5, N 1, p. 18-24.
- 3. D.J. Kim, M.H. Lee, D.Y. Lee, J.S. Han. Mechanical Properties, Phase Stability, and Bio-compatibility of (Y, Nb)-TZP/Al(2)O(3) Composit Abutments for Dental Implant // Journal of Biomedical Materials Research. 2000, v. 53, p. 438-43.
- 4. B.D. Ratner. New Ideas in Biomaterials Science–A Path to Engineered Biomaterials // *Journal of Biomedical Materials Research*. 1993, v. 27, p. 837-850.
- 5. D. Velten, V. Biehl, F. Aubertin, B. Valeske, W. Possart, J. Breme. Preparation of TiO(2) Layers on Cp-Ti and Ti6Al4V by Thermal and Anodic Oxidation and by Sol-gel Coating Techniques and Their Characterization // Journal of Biomedical Materials Research. 2002, v. 59, p. 18-28.
- 6. A.V. Zykova, V.V. Luk'yanchenko, V.I. Safonov. The corrosion properties of implanted materials with protective properties in the isotonic physiological solution // Journal of Surface & Coatings Technology. 2005, v. 200, p.90-93.
- 7. A. Zykova, V. Safonov, O. Virva, V. Luk'yanchenko, J. Walkowich, R. Rogowska, S. Yakovin. Surface parameters modification by multilayer coatings deposition for biomedical applications // Journal of Physics Conference Series. 2008, v. 113, p.1-5.

Article received 8.10.08

КОРРОЗИОННЫЕ СВОЙСТВА МНОГОСЛОЙНЫХ ПОКРЫТИЙ, НАНОСИМЫХ НА НЕРЖАВЕЮЩУЮ СТАЛЬ И ТИТАНОВЫЕ СПЛАВЫ

А. Зыкова, В. Сафонов, J. Walkowich, R. Rogowska, С. Яковин

Нержавеющая сталь и титановые сплавы широко применяются в современной медицине. Поверхностная модификация металлов путем нанесения керамических покрытий современными плазменными методами является перспективным направлением для уменьшения коррозии, повышения биосовместимости и эффективности применения медицинских изделий. Проведен сравнительный анализ следующих свойств пленок: адгезии, твердости, упругих модулей, коррозионных характеристик различных многослойных нитридных и оксидных покрытий.

КОРОЗІЙНІ ВЛАСТИВОСТІ БАГАТОШАРОВИХ ПОКРИТТІВ, ЩО НАНЕСЕНІ НА НЕРЖАВІЮЧУ СТАЛЬ ТА ТИТАНОВІ СПЛАВИ

Г. Зикова, В. Сафонов, J. Walkowich, R. Rogowska, С. Яковін

Нержавіюча сталь та титанові сплави широко використовуються в сучасній медицині. Поверхнева модифікація металів шляхом нанесення керамічних покриттів сучасними плазмовими методами э перспективним напрямком з метою зменшення корозії та покращення біосумісності та ефективності застосування медичних приладів. Виконано порівняльний аналіз наступних властивостей плівок: адгезії, твердості, пружних модулів, корозійних властивостей різних багатошарових оксидних та нітридних покриттів.